



OFFICINE MARIO DORIN SINCE 1918  
**DORIN**<sup>®</sup>  
INNOVATION

**RICAMBI**  
SPARE PARTS

**HEX11**




**SEMI-HERMETIC MOTOR COMPRESSORS**  
**MOTOCOMPRESSORI SEMIERMETICI**



OFFICINE MARIO DORIN SINCE 1918  
**DORIN**  
INNOVATION

M/COMPRESSORE - M/COMPRESSOR  
**HEX11**  
ESPLOSO COMMERCIALE - COMMERCIAL EXPLODED VIEW





OFFICINE MARIO DORIN SINCE 1918  
**DORIN**  
INNOVATION

M/COMPRESSORE - M/COMPRESSOR  
**HEX11**



RIF.	QUANTITA'																CODICE CODE	DESCRIZIONE	DESCRIPTION	
	HEX51CS	HEX80CC	HEX80CS	HEX101CC	HEX101CS	HEX151CC	HEX151CS	HEX181CC	HEX181CS	HEX201CC	HEX201CS	HEX221CC	HEX221CS	HEX251CC	HEX251CS	HEX281CC				HEX281SB
010	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1MKD022	Disco sbattiolio	Oil centrifugal disk
010	-	-	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1MKD023	Disco sbattiolio	Oil centrifugal disk
020	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1CC5024	Kit sospensioni compl.	Vibration damper kit compl.
030	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1CKJ012	Kit bronzine + rasamento	Bushing + thrust kit
040	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1MKA300	Albero completo c.28	Complete shaft c.28
040	-	-	1	1	1	1	-	-	-	-	-	-	-	-	-	-	-	1MKA301	Albero completo c.34	Complete shaft c.34
040	-	-	-	-	-	-	1	1	1	1	-	-	-	-	-	-	-	1MKA302	Albero completo c.38	Complete shaft c.38
040	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	-	1MKA303	Albero completo c.41	Complete shaft c.41
040	-	-	-	-	-	-	-	-	-	-	-	1	1	1	1	-	-	1MKA304	Albero completo c.44	Complete shaft c.44
040	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	1	1MKA305	Albero completo c.50	Complete shaft c.50
050	2	2	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1MCDB89	Kit biella - pistone	Conn.rod. - piston compl.
050	-	-	2	2	-	-	-	-	-	-	-	-	-	-	-	-	-	1MCDB90	Kit biella - pistone	Conn.rod. - piston compl.
050	-	-	-	-	2	2	-	-	-	-	-	-	-	-	-	-	-	1MCDB85	Kit biella - pistone	Conn.rod. - piston compl.
050	-	-	-	-	-	-	2	2	-	-	-	-	-	-	-	-	-	1MCDB86	Kit biella - pistone	Conn.rod. - piston compl.
050	-	-	-	-	-	-	-	-	2	2	-	-	-	-	-	-	-	1MCDB91	Kit biella - pistone	Conn.rod. - piston compl.
050	-	-	-	-	-	-	-	-	-	-	2	2	-	-	-	-	-	1MCDB92	Kit biella - pistone	Conn.rod. - piston compl.
050	-	-	-	-	-	-	-	-	-	-	-	-	2	2	-	-	-	1MCDB93	Kit biella - pistone	Conn.rod. - piston compl.
050	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	-	-	1MCDB94	Kit biella - pistone	Conn.rod. - piston compl.
050	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	1MCDA09	Kit biella - pistone	Conn.rod. - piston compl.
060	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1CCQ020	Spia olio completa	Oil sight glass
070	1	1	1	1	1	1	1	1	1	1	-	-	-	-	-	-	-	1RKA024	Rubinetto di mandata	Discharge service valve
070	-	-	-	-	-	-	-	-	-	-	1	1	1	1	1	1	1	1RKA025	Rubinetto di mandata	Discharge service valve
080	1	1	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	1PKP110	Piastra valvole	Complete valve plate
080	-	-	-	-	1	1	1	1	-	-	-	-	-	-	-	-	-	1PKP111	Piastra valvole	Complete valve plate
080	-	-	-	-	-	-	-	-	1	1	1	1	1	1	-	-	-	1PCB097	Piastra valvole	Complete valve plate
080	-	-	-	-	-	-	-	-	-	-	-	-	-	1	1	1	1	1PCB098	Piastra valvole	Complete valve plate
090	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1RKA024	Rubinetto aspirazione	Suction service valve
090	-	-	1	1	1	1	1	1	1	-	-	-	-	-	-	-	-	1RKA025	Rubinetto aspirazione	Suction service valve
090	-	-	-	-	-	-	-	-	-	1	1	1	1	1	1	1	1	1RKA020	Rubinetto aspirazione	Suction service valve
100	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1RKJ110	Sc. Att. elettrici + piastra	Electrical plate and box
110	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1RKK289	Roto-statore 0,5HP 50Hz	Stator-rotor 0,5HP 50Hz
110	-	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1RKK291	Roto-statore 0,75HP 50Hz	Stator-rotor 0,75HP 50Hz
110	-	-	-	1	1	-	-	-	-	-	-	-	-	-	-	-	-	1RKK292	Roto-statore 1HP 50Hz	Stator-rotor 1HP 50Hz
110	-	-	-	-	-	1	1	-	-	-	-	-	-	-	-	-	-	1RKK293	Roto-statore 1,5HP 50Hz	Stator-rotor 1,5HP 50Hz
110	-	-	-	-	-	-	1	1	-	1	-	-	-	-	-	-	-	1RKK294	Roto-statore 1,8HP 50Hz	Stator-rotor 1,8HP 50Hz
110	-	-	-	-	-	-	-	-	1	-	1	1	-	1	-	1	-	1RKK295	Roto-statore 3HP 50Hz	Stator-rotor 3HP 50Hz
110	-	-	-	-	-	-	-	-	-	-	-	-	1	-	1	-	1	1RKK296	Roto-statore 3,5HP 50Hz	Stator-rotor 3,5HP 50Hz
110	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1RKK300	Roto-statore 0,6HP 60Hz	Stator-rotor 0,6HP 60Hz
110	-	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1RKK301	Roto-statore 0,9HP 60Hz	Stator-rotor 0,9HP 60Hz
110	-	-	-	1	1	-	-	-	-	-	-	-	-	-	-	-	-	1RKK302	Roto-statore 1,2HP 60Hz	Stator-rotor 1,2HP 60Hz
110	-	-	-	-	-	1	1	-	-	-	-	-	-	-	-	-	-	1RKK303	Roto-statore 1,8HP 60Hz	Stator-rotor 1,8HP 60Hz
110	-	-	-	-	-	-	1	1	-	1	-	-	-	-	-	-	-	1RKK304	Roto-statore 2,1HP 60Hz	Stator-rotor 2,1HP 60Hz
110	-	-	-	-	-	-	-	-	1	-	1	1	-	1	-	1	-	1RKK305	Roto-statore 3,6HP 60Hz	Stator-rotor 3,6HP 60Hz
110	-	-	-	-	-	-	-	-	-	-	-	-	1	-	1	-	1	1RKK306	Roto-statore 4,2HP 60Hz	Stator-rotor 4,2HP 60Hz



OFFICINE MARIO DORIN SINCE 1918  
**DORIN**  
INNOVATION

M/COMPRESSORE - M/COMPRESSOR  
**HEX11**



RIF.	QUANTITA'																CODICE CODE	DESCRIZIONE	DESCRIPTION		
	HEX51CS	HEX80CC	HEX80CS	HEX101CC	HEX101CS	HEX151CC	HEX151CS	HEX181CC	HEX181CS	HEX201CC	HEX201CS	HEX221CC	HEX221CS	HEX251CC	HEX251CS	HEX281CC				HEX281SB	HEX281CS
<b>ACCESSORI - ACCESSORIES</b>																					
	1	1	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1CCM160	Serie completa guarnizioni	Complete gasket set
	-	-	-	-	1	1	1	1	-	-	-	-	-	-	-	-	-	-	1CCM161	Serie completa guarnizioni	Complete gasket set
	-	-	-	-	-	-	-	-	1	1	1	1	1	1	-	-	-	-	1CCM162	Serie completa guarnizioni	Complete gasket set
	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	1	1	1	1CCM163	Serie completa guarnizioni	Complete gasket set
	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1CCT024	Testa raffreddata ad acqua	Water-cooled head
	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2EG2020	Resistenza carter 220V	Crankcase heater 220V
	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2EG1050	Resistenza carter 110V	Crankcase heater 110V
	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2EG1080	Resistenza carter 24V	Crankcase heater 24V
	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2CC3110	Modulo per termistori	Thermistors module
	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2CG1070	Sonda temp. di scarico	Discharge temp.probe



OFFICINE MARIO DORIN SINCE 1918  
**DORIN**  
INNOVATION

OFFICINE MARIO DORIN S.p.A.  
Via Aretina 388, 50061 Compiobbi - Florence, Italy  
Tel. +39 055 62321 1 - Fax +39 055 62321 380

dorin@dorin.com  
www.dorin.com

HEX11 COMM.  
REV.01